

Aquamatic 5200

Grain Moisture Meter



Benefits:

Superior Accuracy
Moisture and Specific Weight
10s analysis
Touch screen operation

Aquamatic 5200 Grain Moisture Meter

The AM 5200 is Perten's second-generation high frequency moisture meter. Drawing on the experience from more than 1,000 installed units, we have designed a moisture meter improved in every aspect – accuracy, repeatability, reliability, and user interface. It can be a stand-alone moisture meter for use at terminals or can be integrated into automated testing systems.

Higher frequencies provide greater penetration of samples; the updated UGMA provides a more accurate result regardless of temperature or crop type; the improved mechanism provides better repeatability. Together this make the AM 5200 the most accurate and repeatable moisture meter available. It can analyze grains, oilseeds, pulses, beans, lentils, seeds and more for moisture, Test Weight/Hectoliter Weight, and temperature.

Features and Benefits

Superior Accuracy: Superior accuracy and repeatability are obtained using 150 MHz measurement cell made of robust, high precision die-cast aluminum. The new cell is slightly larger providing a more representative sample.

Accurate Results on Fresh Field Samples: Older moisture meters read up to 1% low in moisture when analyzing grain straight from the field (known as the rebound effect). The higher frequency measurement employed by the AM 5200 penetrates deeper into the grain providing more accurate results and shorter return of investment.

Easy To Use: The large color touch screen with intuitive user interface makes the AM 5200 simple to use. Input sample IDs, view results on a remote screen, and update through USB memory sticks all add to its flexibility and ease of use. The touchscreen uses resistance technology and will even respond to gloved hands.

Rapid Analysis: Just pour the sample and the AM 5200 begins analysis automatically. Results are displayed in less than 10 seconds. An optional flow-through provides for automated testing when the sample can be discarded.

Modern Technology: Using higher frequency, advanced computational power, USB data transfer, and the updated UGMA, the AM 5200 is designed for today's grain trade.

Specifications

Products: Grains, oilseeds, pulses, lentils and more

Parameters: Moisture, specific weight (hectoliter weight/test weight) and temperature

Analysis Time: ~ 10 seconds

Display: 5.7" color touch screen

Connectivity: Ethernet, USB

Measurement Technique: RF dielectric constant at 150 Mhz

Sample Temperature: 0-40° C / 32-100 F

Sample Size: 700 ml

Power Requirement: 115/230 V, 50/60 Hz

Dimensions H x W x D (mm/inches): 415/16.3 x 424/16.7 x 353/13.9

Net Weight (kg/lb): 18.3/40.3